

Product data sheet

Characteristics

56/2PBS1-RO

56 Series IP66 emergency STOP/START - Resistance Orange



Main

Range of product	Series 56
Product brand	Clipsal

Complementary

[Us] rated supply voltage	Lamp: 250 V AC
[In] rated current	10 A
Colour	Resistant orange
Cap/operator or lens colour	Red/green
Width	101 mm opening:
Height	107 mm opening:
Depth	80 mm opening:
Marking	START-STOP

Environment

IP degree of protection	IP66
-------------------------	------

Packing Units

Package 1 Weight	0.400 kg
------------------	----------

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.