

Product data sheet

Characteristics

56/2PBS1LE-GY

Push Button Control Station, Clipsal - 56 Series, 10A, IP66, Less Enclosure

Main

Range of product	Series 56
Product brand	Clipsal

Complementary

[Us] rated supply voltage	Lamp: 250 V AC
[In] rated current	10 A
Colour	Grey
Cap/operator or lens colour	Red/green
Width	Opening: 101 mm
Height	Opening: 107 mm
Depth	Opening : 80 mm
Marking	START-STOP


Environment

IP degree of protection	IP66
-------------------------	------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	0.25 kg

Offer Sustainability

EU RoHS Directive	Compliant with Exemptions
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.