

Product data sheet

Characteristics

56/2PBS1LE-GY

CONTROL STN IP66 EM SP/ST LESS ENCLOSURE



Main

Range of product	Series 56
Product brand	Clipsal

Complementary

[Us] rated supply voltage	Lamp: 250 V AC
[In] rated current	10 A
Colour	Grey
Cap/operator or lens colour	Red/green
Width	101 mm opening:
Height	107 mm opening:
Depth	80 mm opening:
Marking	START-STOP

Environment

IP degree of protection	IP66
-------------------------	------

Packing Units

Package 1 Weight	0.250 kg
------------------	----------

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile