

Product data sheet

Characteristics

56/32-CG

56 Series Socket - Accessory



Main

Range of product	Series 56
Range	Clipsal - 56 Series
Product brand	Clipsal
Plug, socket category	Low voltage
Outlet standard	Industrial
Colour	Grey (RAL 7035)
Cover type	Transparent

Complementary

Number of gangs	2 gangs
Shape	Square
Device mounting	Surface
Cable entry number	2
Material	ABS (acrylonitrile butadiene-styrene): cover
Fixing mode	By screws
Tightening torque	0.8 N.m
Length	107 mm
Width	101 mm
Depth	77 mm
Height	107 mm
Net weight	0.389 kg
IP degree of protection	IP66
Targeted country	Australia

Environment

Ambient air temperature for operation	-25...75 °C
---------------------------------------	-------------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	10.7 cm
Package 1 Width	10.1 cm
Package 1 Length	7.7 cm
Package 1 Weight	0.389 kg

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile