

Product data sheet

Characteristics

56/32-GY

Clipsal - 56 Series, Aperture Enclosure, 2 Gang



Main

Range of product	Series 56
Range	Clipsal - 56 Series
Product brand	Clipsal
Product or component type	Enclosure
Plug, socket category	Low voltage
Outlet standard	Industrial
Colour	Grey (RAL 7035)
Cover type	Transparent

Complementary

Number of gangs	2 gangs
Shape	Square
Device mounting	Surface
Cable entry number	2
Material	Polycarbonate: cover
Fixing mode	By screws
Tightening torque	0.8 N.m
Length	107 mm
Width	101 mm
Depth	77 mm
Height	107 mm
Net weight	0.36 kg
IP degree of protection	IP66
Targeted country	Australia




Environment

Ambient air temperature for operation	-25...75 °C
---------------------------------------	-------------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	8.8 cm
Package 1 Width	10.8 cm
Package 1 Length	10.9 cm
Package 1 Weight	362.0 g
Unit Type of Package 2	CAR
Number of Units in Package 2	24
Package 2 Height	21.4 cm
Package 2 Width	29.7 cm
Package 2 Length	42.9 cm
Package 2 Weight	9.192 kg

Offer Sustainability

REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes