

Product data sheet

Characteristics

56/32LE-GY

56 Series Socket - Accessory



Main

Range of product	Series 56
Range	Clipsal - 56 Series
Product brand	Clipsal
Plug, socket category	Low voltage
Outlet standard	Industrial
Colour	Grey (RAL 7035)
Cover type	Without screening Transparent
Lock type	Possibility to seal it
Enclosure type	Weatherproof enclosure

Complementary

Number of gangs	2 gangs
Shape	Rectangular
Device mounting	Surface
Product destination	Diameter: 20 mm tube
Location of connection	Rear
Tracks	No track
Material	Polycarbonate: cover
Surface finish	Bare
Fixing mode	By screws
Tightening torque	0.8 N.m
Length	107 mm
Width	101 mm
Depth	39 mm
Height	107 mm
Net weight	0.176 kg
IP degree of protection	IP66
Targeted country	Australia

Environment

Ambient air temperature for operation	-25...75 °C
---------------------------------------	-------------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	180.0 g
Package 1 Height	7 cm
Package 1 width	10.2 cm
Package 1 Length	10 cm
Unit Type of Package 2	PAL
Number of Units in Package 2	1215
Package 2 Weight	247840.0 g
Package 2 Height	106.5 cm

Package 2 width	116.5 cm
Package 2 Length	116.5 cm
Unit Type of Package 3	CAR
Number of Units in Package 3	45
Package 3 Weight	8100.0 g
Package 3 Height	30.5 cm
Package 3 width	29.6 cm
Package 3 Length	43.6 cm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile