

## Product data sheet

### Characteristics

# 56AI520LE-EO

## SOCKET APPLIANCE INLET IP56 5 PIN LESS ENCLOSURE



### Main

Range of product	Series 56
Product brand	Clipsal

### Complementary

[In] rated current	20 A
[Ue] rated operational voltage	500 V 50/60 Hz conforming to EN 60309-2
Colour	Electric orange
Material	Plastic
Connections - terminals	Screw terminal
Plug, socket, control station shape	Angled
Duration	7 h

### Packing Units

Package 1 Weight	0.417 kg
------------------	----------

### Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.