

## Product data sheet

### Characteristics

# 56C310/4EL-GY

Clipsal - 56 Series, RCD Protected Socket Outlet, 250V, 10A, 3 Flat PIN, IP66, 30mA Surface Mount



### Main

Range of product	Series 56
Product brand	Clipsal
Product or component type	Socket-outlet with residual current device
Device application	Power supply
Colour	Grey (RAL 7035)

### Complementary

Number of poles	3
Number of power socket outlets	1 protective cover
[In] rated current	10 A
[Ue] rated operational voltage	250 V AC
Device mounting	Surface
Material	PVC (polyvinyl chloride): housing
Depth	135 mm
Width	101 mm
Height	300 mm

### Environment

Earth-leakage protection class	Class A
--------------------------------	---------

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	11.3 cm
Package 1 Width	10.3 cm
Package 1 Length	30.0 cm
Package 1 Weight	1411.0 g
Unit Type of Package 2	CAR
Number of Units in Package 2	8
Package 2 Height	30.5 cm
Package 2 Width	29.6 cm
Package 2 Length	43.6 cm
Package 2 Weight	11.288 kg

Offer Sustainability

REACH Regulation	 <a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant with Exemptions
China RoHS Regulation	 <a href="#">China RoHS Declaration</a>
RoHS exemption information	 <a href="#">Yes</a>