

Product data sheet

Characteristics

56C310/4EL-GY

56 Series switched socket surface IP66 RCD 3 pin 10 A - Grey



Main

Range of product	Series 56
Product brand	Clipsal
Product or component type	Socket-outlet with residual current device
Device application	Power supply
Colour	Grey (RAL 7035)

Complementary

Number of poles	3
Number of power socket outlets	1 protective cover
[In] rated current	10 A
[Ue] rated operational voltage	250 V AC
Device mounting	Surface
Material	PVC (polyvinyl chloride): housing
Depth	135 mm
Width	101 mm
Height	300 mm

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	1411.0 g
Package 1 Height	11.3 cm
Package 1 width	10.3 cm
Package 1 Length	30 cm
Unit Type of Package 2	CAR
Number of Units in Package 2	8
Package 2 Weight	11.288 kg
Package 2 Height	30.5 cm
Package 2 width	29.6 cm
Package 2 Length	43.6 cm

Offer Sustainability

Sustainable offer status	Green Premium product
RECh Regulation	 RECh Declaration
EU RoHS Directive	Compliant  EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	 Yes

China RoHS Regulation

 [China RoHS Declaration](#)

Environmental Disclosure

 [Product Environmental Profile](#)
