

## Product data sheet

### Characteristics

# 56C310EL2P-GY

Clipsal - 56 Series, RCBO Protected Switched Socket Outlet, 250V, 10A, 3 Flat PIN, IP56, 30mA RCBO



### Main

Range of product	Series 56
Product brand	Clipsal
Product or component type	Socket-outlet with residual current device
Device application	Power supply
Colour	Grey (RAL 7035)

### Complementary

Number of poles	3
Number of power socket outlets	2 protective cover
[In] rated current	10 A
[Ue] rated operational voltage	250 V AC
Material	PVC (polyvinyl chloride): housing
Electrical connection	Power cord
Depth	105 mm
Width	294 mm
Height	243 mm

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	26 cm
Package 1 Width	26 cm
Package 1 Length	40 cm
Package 1 Weight	3.04 kg

### Offer Sustainability

Sustainable offer status	Green Premium product
RECh Regulation	<a href="#">RECh Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>