

## Product data sheet

### Characteristics

# 56C310EL2P-GY

56 Series switched socket IP66 portable RCD 3 pin 10 A - Grey



### Main

Range of product	Series 56
Product brand	Clipsal
Product or component type	Socket-outlet with residual current device
Device application	Power supply
Colour	Grey (RAL 7035)

### Complementary

Number of poles	3
Number of power socket outlets	2 protective cover
[In] rated current	10 A
[Ue] rated operational voltage	250 V AC
Material	PVC (polyvinyl chloride): housing
Electrical connection	Power cord
Depth	105 mm
Width	294 mm
Height	243 mm

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	3.04 kg
Package 1 Height	260 mm
Package 1 width	260 mm
Package 1 Length	400 mm
Unit Type of Package 2	CAR
Number of Units in Package 2	2
Package 2 Weight	6.2 kg
Package 2 Height	238 mm
Package 2 width	342 mm
Package 2 Length	390 mm
Unit Type of Package 3	PAL
Number of Units in Package 3	60
Package 3 Weight	182.4 kg

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

## Offer Sustainability

Sustainable offer status	Green Premium product
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>