

Product data sheet

Characteristics

56C310EL2P-RO

RCBO Protected Switched Socket Outlet,
Clipsal - 56 Series, 250V, 10A, 3 Flat PIN,
IP56, 30mA



Main

Range of product	Series 56
Product brand	Clipsal
Product or component type	Socket-outlet with residual current device
Device application	Power supply
Colour	Resistant orange

Complementary

Number of poles	3
Number of power socket outlets	2 protective cover
[In] rated current	10 A
[Ue] rated operational voltage	250 V AC
Material	PVC (polyvinyl chloride): housing
Electrical connection	Power cord
Depth	105 mm
Width	294 mm
Height	243 mm

Environment

Earth-leakage protection class	Class A
--------------------------------	---------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	26.0 cm
Package 1 Width	26.0 cm
Package 1 Length	40.0 cm
Package 1 Weight	3.1 kg
Unit Type of Package 2	CAR
Number of Units in Package 2	2
Package 2 Height	23.8 cm
Package 2 Width	34.2 cm
Package 2 Length	39.0 cm
Package 2 Weight	6.2 kg

Offer Sustainability

REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant with Exemptions
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes