

## Product data sheet

### Characteristics

# 56C315/4EL-GY

Clipsal - 56 Series, Switched Socket Outlet  
250V, 15A, 3 Flat PIN, IP66, Surface Mount,  
Earth Leakage



#### Main

Range of product	Series 56
Product brand	Clipsal
Product or component type	Socket-outlet with residual current device
Device application	Power supply
Colour	Grey (RAL 7035)

#### Complementary

Number of poles	3
Number of power socket outlets	1 protective cover
[In] rated current	15 A
[Ue] rated operational voltage	250 V AC
Device mounting	Surface
Material	PVC (polyvinyl chloride): housing
Depth	100 mm
Width	101 mm
Height	204 mm

#### Environment

Earth-leakage protection class	Class A
--------------------------------	---------

#### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	11.3 cm
Package 1 Width	10.5 cm
Package 1 Length	30.0 cm
Package 1 Weight	1413.0 g
Unit Type of Package 2	CAR
Number of Units in Package 2	8
Package 2 Height	30.5 cm
Package 2 Width	29.6 cm
Package 2 Length	43.6 cm
Package 2 Weight	12.0 kg

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>