

## Product data sheet

### Characteristics

# 56C420LE-RO

## Switched Socket, Clipsal - 56 Series, Surface IP66 4 PIN 20A Less Enclosure

### Main

Range of product	Series 56
Range	Clipsal - 56 Series
Product brand	Clipsal
Product or component type	Socket-outlet
Device application	Power supply
Colour	Orange (RAL 2004)

### Complementary

Number of poles	4
Plug, socket category	Low voltage
Outlet standard deviation	Australian/New Zealand
Plug, socket, control station shape	Straight
Number of modules	3
Number of power socket outlets	1 protective cover
[In] rated current	20 A
[Ue] rated operational voltage	500 V AC 50 Hz
Poles description	3P + E
Protection type	Without protection
Device mounting	Surface
Material	PC + PET: cover
Contacts material	Pins: phosphor bronze
Connections - terminals	Screw terminals cable(s) 2.5...6 mm <sup>2</sup>
Electrical connection	Industrial connector
Depth	45 mm
Width	101 mm
Height	198 mm
Targeted country	Australia

### Environment




Standards	AS/NZS 3123 AS/NZS 3133
Ambient air temperature for operation	-25...75 °C
IP degree of protection	IP66 conforming to AS 60529

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4.5 cm
Package 1 Width	10.1 cm
Package 1 Length	19.8 cm

Package 1 Weight	0.667 kg
Unit Type of Package 2	CAR
Number of Units in Package 2	12
Package 2 Height	21.0 cm
Package 2 Width	34.8 cm
Package 2 Length	44.5 cm
Package 2 Weight	8.004 kg

### Offer Sustainability

Packaging without single use plastic	No
Packaging made with recycled cardboard	Yes
REACH Regulation	 <a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant with Exemptions
RoHS exemption information	 <a href="#">Yes</a>
China RoHS Regulation	 <a href="#">China RoHS Declaration</a>
Take-back	No