

Product data sheet

Characteristics

56C432-CG

Switched Socket Outlet, 500V, 32A, 4 Round PIN, IP66, 3 Pole, 32A



Main

Range of product	Series 56
Range	Clipsal - 56 Series
Product brand	Clipsal
Product or component type	Socket-outlet
Device application	Power supply
Colour	Chemical grey

Complementary

Number of poles	4
Plug, socket category	Low voltage
Outlet standard deviation	Australian/New Zealand
Plug, socket, control station shape	Straight
Number of modules	3
Number of power socket outlets	1 protective cover
[In] rated current	32 A
[Ue] rated operational voltage	500 V AC 50 Hz
Poles description	3P + E
Protection type	Without protection
Device mounting	Surface
Material	ABS (acrylonitrile butadiene-styrene): cover
Contacts material	Pins: phosphor bronze
Connections - terminals	Screw terminals cable(s) 6...16 mm ²
Electrical connection	Industrial connector
Depth	108 mm
Width	101 mm
Height	204 mm
Targeted country	Australia

Environment

Standards	AS/NZS 3123 AS/NZS 3133
Ambient air temperature for operation	-25...75 °C
IP degree of protection	IP66 conforming to AS 60529

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Packing Units

Unit Type of Package 1	Db
Number of Units in Package 1	1
Package 1 Height	10.8 cm
Package 1 Width	10.1 cm
Package 1 Length	20.4 cm
Package 1 Weight	1.26 kg
Unit Type of Package 2	CAR
Number of Units in Package 2	12
Package 2 Height	21.0 cm
Package 2 Width	34.8 cm
Package 2 Length	44.5 cm
Package 2 Weight	15.12 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile