

Product data sheet

Characteristics

56C520RC-GY

RCD Protected Switched Socket Outlet, 500V, 20A, 5 Round PIN, IP66, 3 Pole



Main

Range of product	Series 56
Range	Clipsal - 56 Series
Product brand	Clipsal
Product or component type	Socket-outlet with residual current device
Device application	Power supply
Colour	Grey (RAL 7035)

Complementary

Number of poles	5
Control type	Push-button
Number of power socket outlets	1 protective cover
[In] rated current	20 A
[Ue] rated operational voltage	500 V AC 50 Hz
Network number of phases	3 phases
Number of gangs	3 gangs
Installation direction	Vertical
Device mounting	Surface
Material	Polycarbonate
Connections - terminals	Screw terminals cable(s) 1.5...16 mm ²
Depth	110 mm
Width	101 mm
Height	294 mm
Net weight	1.64 kg
Targeted country	Australia

Environment

Ambient air temperature for operation	-25...75 °C
IP degree of protection	IP66

Packing Units

Unit Type of Package 1	Db
Number of Units in Package 1	1
Package 1 Height	11.5 cm
Package 1 Width	10.2 cm
Package 1 Length	30.0 cm
Package 1 Weight	1632.5 g

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile