

## Product data sheet

### Characteristics

# 56C540RC-GY

## Clipsal - 56 Series, Switched Socket RCD



### Main

Range	Clipsal - 56 Series
Product or component type	Socket-outlet with residual current device
Device application	Power supply
Colour	Grey (RAL 7035)

### Complementary

Control type	Push-button
[In] rated current	40 A
[Ue] rated operational voltage	500 V AC 50 Hz
Network number of phases	3 phases
Number of gangs	3 gangs
Installation direction	Vertical
Material	Polycarbonate
Connections - terminals	Screw terminal cable(s) 10...16 mm <sup>2</sup>
Mounting mode	Surface mounted
Depth	110 mm
Width	101 mm
Height	294 mm
Net weight	1.88 kg
Targeted country	Australia

### Environment

Ambient air temperature for operation	-25...75 °C
IP degree of protection	IP66

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	11.5 cm
Package 1 Width	10.0 cm
Package 1 Length	30.0 cm
Package 1 Weight	1802.0 g
Unit Type of Package 2	CAR
Number of Units in Package 2	5
Package 2 Height	30.0 cm
Package 2 Width	23.0 cm
Package 2 Length	37.0 cm
Package 2 Weight	11.0 kg

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>