

## Product data sheet

### Characteristics

# 56C540RC-GY

## 56 Series Socket Outlet with RCD - 40A - 5 Pin - 500V - 30mA RCD - Grey



### Main

Range	Clipsal - 56 Series
Product or component type	Socket-outlet with residual current device
Device application	Power supply
Colour	Grey (RAL 7035)

### Complementary

Control type	Push-button
[In] rated current	40 A
[Ue] rated operational voltage	500 V AC 50 Hz
Network number of phases	3 phases
Number of gangs	3 gangs
Installation direction	Vertical
Material	Polycarbonate
Connections - terminals	Screw terminal cable(s) 10...16 mm <sup>2</sup>
Mounting mode	Surface mounted
Depth	110 mm
Width	101 mm
Height	294 mm
Net weight	1.88 kg
Targeted country	Australia

### Environment

Ambient air temperature for operation	-25...75 °C
IP degree of protection	IP66

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	1802 g
Package 1 Height	115 mm
Package 1 width	100 mm
Package 1 Length	300 mm

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

## Offer Sustainability

Sustainable offer status	Green Premium product
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>