

Product data sheet

Characteristics

56C710LE-RO

SWITCHED SOCKET SURFACE IP66 7 PIN

10A LESS ENCLOSURE



Main

Range of product	Series 56
Product brand	Clipsal
Device application	Power supply
Colour	Resistant orange

Complementary

Number of poles	7
Number of modules	3
Number of power socket outlets	1 protective cover
[In] rated current	50 A
[Ue] rated operational voltage	500 V AC
Depth	45 mm
Width	101 mm
Height	198 mm

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4.5 cm
Package 1 Width	10.1 cm
Package 1 Length	19.8 cm
Package 1 Weight	0.001 kg