

Product data sheet

Characteristics

56C710LE-RO

SWITCHED SOCKET SURFACE IP66 7 PIN 10A LESS ENCLOSURE



Main

Range of product	Series 56
Product brand	Clipsal
Device application	Power supply
Colour	Resistant orange

Complementary

Number of poles	7
Number of modules	3
Number of power socket outlets	1 protective cover
[In] rated current	50 A
[Ue] rated operational voltage	500 V AC
Depth	45 mm
Width	101 mm
Height	198 mm

Packing Units

Package 1 Weight	0.001 kg
Package 1 Height	45.000 mm
Package 1 width	101.000 mm
Package 1 Length	198.000 mm

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.