

## Product data sheet

### Characteristics

# 56C720LE-GY

## 56 Series Socket Outlet - 20A - 7 Pin - 3P - 500V - Less Enclosure - Grey



### Main

|                           |                     |
|---------------------------|---------------------|
| Range of product          | Series 56           |
| Range                     | Clipsal - 56 Series |
| Product brand             | Clipsal             |
| Product or component type | Socket-outlet       |
| Device application        | Power supply        |
| Colour                    | Grey (RAL 7035)     |

### Complementary

|                                     |                        |
|-------------------------------------|------------------------|
| Number of poles                     | 7                      |
| Plug, socket category               | Low voltage            |
| Outlet standard                     | Australian/New Zealand |
| Plug, socket, control station shape | Straight               |
| Number of modules                   | 3                      |
| Number of power socket outlets      | 1 protective cover     |
| [In] rated current                  | 20 A                   |
| [Ue] rated operational voltage      | 500 V AC 50 Hz         |
| Poles description                   | 3P + N + E             |
| Protection type                     | Without protection     |
| Device mounting                     | Surface                |
| Material                            | Polycarbonate: cover   |
| Contacts material                   | Pins: phosphor bronze  |
| Electrical connection               | Industrial connector   |
| Depth                               | 45 mm                  |
| Width                               | 101 mm                 |
| Height                              | 198 mm                 |
| Targeted country                    | Australia              |

### Environment

|                                       |                             |
|---------------------------------------|-----------------------------|
| Standards                             | AS/NZS 3133<br>AS/NZS 3123  |
| Ambient air temperature for operation | -25...75 °C                 |
| IP degree of protection               | IP66 conforming to AS 60529 |

### Packing Units

|                  |            |
|------------------|------------|
| Package 1 Weight | 0.001 kg   |
| Package 1 Height | 45.000 mm  |
| Package 1 width  | 101.000 mm |
| Package 1 Length | 198.000 mm |

## Offer Sustainability

|                            |   |
|----------------------------|---|
| Sustainable offer status   | Green Premium product                         |
| REACH Regulation           | <a href="#">REACH Declaration</a>             |
| EU RoHS Directive          | Compliant <a href="#">EU RoHS Declaration</a> |
| Mercury free               | Yes   |
| RoHS exemption information | <a href="#">Yes</a>                           |
| China RoHS Regulation      | <a href="#">China RoHS Declaration</a>        |
| Environmental Disclosure   | <a href="#">Product Environmental Profile</a> |