

Product data sheet

Characteristics

56CB4N-CG

Mounting Cover Kit, Clipsal - 56 Series, 4
Module, with 240/415V Neon



Main

Range	Clipsal - 56 Series
Range of product	Series 56
Product brand	Clipsal
Product or component type	DIN cover
Colour	Chemical grey

Complementary

Material	ABS (acrylonitrile butadiene-styrene); housing
Device mounting	Surface
Mounting mode	Wall-mounted
Width	95 mm
Height	190 mm
Depth	50 mm
Net weight	0.33 kg

Environment

Standards	AS 3100
IP degree of protection	IP66 conforming to AS 60529
Ambient air temperature for operation	-25...75 °C

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	5.4 cm
Package 1 Width	10.1 cm
Package 1 Length	20.1 cm
Package 1 Weight	306.0 g
Unit Type of Package 2	CAR
Number of Units in Package 2	14
Package 2 Height	39.5 cm
Package 2 Width	10.2 cm
Package 2 Length	31.0 cm
Package 2 Weight	4.284 kg

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Offer Sustainability

REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes