

Product data sheet

Characteristics

56CB4N-GY

Clipsal - 56 Series, Mounting Cover Kit, 4 Module, with 240/415V Neon



Main

Range	Clipsal - 56 Series
Range of product	Series 56
Product brand	Clipsal
Product or component type	DIN cover
Colour	Grey (RAL 7035)

Complementary

Material	PC + PET: housing
Device mounting	Surface
Mounting mode	Wall-mounted
Width	95 mm
Height	190 mm
Depth	50 mm
Net weight	0.3 kg

Environment

Standards	AS 3100
IP degree of protection	IP66 conforming to AS 60529
Ambient air temperature for operation	-25...75 °C

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	5.3 cm
Package 1 Width	9.9 cm
Package 1 Length	20.0 cm
Package 1 Weight	302.0 g
Unit Type of Package 2	CAR
Number of Units in Package 2	14
Package 2 Height	39.5 cm
Package 2 Width	10.2 cm
Package 2 Length	38.1 cm
Package 2 Weight	4.462 kg

Offer Sustainability

REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes