

Product data sheet

Characteristics

56CSC315-EO

Cord Extension Socket, Clipsal - 56 Series, 3 Flat PIN, 250V, 15A



Main

Range of product	Series 56
Range	Clipsal - 56 Series
Product brand	Clipsal
Product or component type	Socket
Device application	Power supply
Colour	Orange (RAL 2004)

Complementary

Plug, socket category	Low voltage
Plug, socket, control station shape	Straight
Mounting mode	External mounting
[In] rated current	15 A
[Ue] rated operational voltage	250 V AC 50 Hz conforming to EN 60309-2
Poles description	1P + N + E
Voltage colour	Blue
Duration	6 h
Material	Polycarbonate: housing
Contacts material	Sleeves: brass
Connections - terminals	Screw terminals 0.75...1.5 mm ²
Connections - terminals	Screw terminal
Socket number	1
Socket-outlet type	B
Outlet standard	Industrial
Cable outer diameter	7...16 mm
Cable entry	Cable gland
Thread type	M20
Net weight	0.139 kg
Depth	120 mm
Length	105 mm
Width	85 mm
Height	85 mm
Targeted country	Australia

Environment

IP degree of protection	IP66 conforming to AS 60529
Ambient air temperature for operation	-25...75 °C
Standards	AS/NZS 3120

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	6.5 cm
Package 1 Width	6.5 cm
Package 1 Length	10.5 cm
Package 1 Weight	120 g

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant with Exemptions
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations