

## Product data sheet

### Characteristics

# 56CSC332-EO

## 56 Series Socket Connector - 3 Pin - 32A - 250V



### Main

Range of product	Series 56
Range	Clipsal - 56 Series
Product brand	Clipsal
Product or component type	Socket
Device application	Power supply
Colour	Orange (RAL 2004)

### Complementary

Plug, socket category	Low voltage
Plug, socket, control station shape	Straight
Mounting mode	External mounting
[In] rated current	32 A
[Ue] rated operational voltage	250 V AC 50 Hz conforming to EN 60309-2
Poles description	1P + N + E
Voltage colour	Blue
Duration	6 h
Material	Polycarbonate: housing
Contacts material	Sleeves: brass
Connections - terminals	Screw terminals 2.5...25 mm <sup>2</sup>
Connections - terminals	Screw terminal
Socket number	1
Socket-outlet type	I
Outlet standard	Industrial
Cable outer diameter	9...29 mm
Cable entry	Cable gland
Thread type	M40
Net weight	0.366 kg
Depth	180 mm
Length	184 mm
Width	90 mm
Height	90 mm
Targeted country	Australia

### Environment

IP degree of protection	IP66 conforming to AS 60529
Ambient air temperature for operation	-25...75 °C
Standards	AS/NZS 3120

## Packing Units

Package 1 Weight	419.000 g
Package 1 Height	95.000 mm
Package 1 width	95.000 mm
Package 1 Length	200.000 mm

## Offer Sustainability

Sustainable offer status	Green Premium product
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>