

Product data sheet

Characteristics

56CTC2SO15-GY

SOCKET OUTLET SWITCH TIMER TWIN.

TEMPERATURE RANGE -25C TO +75C



Main

Range of product	Series 56
Product brand	Clipsal
Device application	Power supply
Colour	Grey (RAL 7035)

Complementary

Number of poles	3
Number of modules	1
Number of power socket outlets	2 protective cover
[In] rated current	15 A
[Ue] rated operational voltage	250 V AC
Device mounting	Surface
Number of plates	1
Material	PVC (polyvinyl chloride): housing
Depth	100 mm
Width	198 mm
Height	204 mm

Packing Units

Package 1 Weight	0.001 kg
Package 1 Height	100.000 mm
Package 1 width	198.000 mm
Package 1 Length	204.000 mm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant  EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	 Yes
China RoHS Regulation	 China RoHS Declaration
Environmental Disclosure	 Product Environmental Profile
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins