

## Product data sheet

### Characteristics

# 56CV310-GY

Clipsal - 56 Series, Switched Socket Outlet, 250V, 10A, 3 Flat PIN, IP66, 1 Pole, Vertical



### Main

Range of product	Series 56
Range	Clipsal - 56 Series
Product brand	Clipsal
Product or component type	Socket-outlet
Device application	Power supply
Colour	Grey (RAL 7035)

### Complementary

Number of poles	3
Plug, socket category	Low voltage
Outlet standard	Australian/New Zealand
Plug, socket, control station shape	Straight
Number of modules	1
Number of power socket outlets	1 protective cover
[In] rated current	10 A
[Ue] rated operational voltage	250 V AC 50 Hz
Poles description	1P + N + E
Protection type	Without protection
Device mounting	Surface
Material	Polycarbonate: cover
Contacts material	Pins: phosphor bronze
Connections - terminals	Screw terminals cable(s) 1.5...6 mm <sup>2</sup>
Depth	83 mm
Width	101 mm
Height	204 mm
Targeted country	Australia

### Environment


Standards	AS/NZS 3112 AS/NZS 4417.1
Ambient air temperature for operation	-25...75 °C
IP degree of protection	IP66 conforming to AS 60529

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	8.9 cm
Package 1 Width	10.3 cm
Package 1 Length	20.5 cm
Package 1 Weight	699.0 g

Unit Type of Package 2	CAR
Number of Units in Package 2	12
Package 2 Height	21.4 cm
Package 2 Width	29.7 cm
Package 2 Length	42.9 cm
Package 2 Weight	8.496 kg

### Offer Sustainability

REACH Regulation	 <a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant with Exemptions
China RoHS Regulation	 <a href="#">China RoHS Declaration</a>
RoHS exemption information	 <a href="#">Yes</a>