

Product data sheet

Characteristics

56CV310LE-GY

Switched Socket, Clipsal - 56 Series, Vertical
IP66 3 PIN 10A Less Enclosure

Main

Range of product	Series 56
Range	Clipsal - 56 Series
Product brand	Clipsal
Product or component type	Socket-outlet
Device application	Power supply
Colour	Grey (RAL 7035)

Complementary

Number of poles	3
Plug, socket category	Low voltage
Outlet standard deviation	Australian/New Zealand
Plug, socket, control station shape	Straight
Number of modules	1
Number of power socket outlets	1 protective cover
[In] rated current	10 A
[Ue] rated operational voltage	250 V AC 50 Hz
Poles description	1P + N + E
Protection type	Without protection
Device mounting	Surface
Material	Polycarbonate: cover
Contacts material	Pins: phosphor bronze
Connections - terminals	Screw terminals cable(s) 1.5...6 mm ²
Depth	45 mm
Width	101 mm
Height	198 mm
Targeted country	Australia

Environment

Standards	AS/NZS 3112 AS/NZS 4417.1
Ambient air temperature for operation	-25...75 °C
IP degree of protection	IP66 conforming to AS 60529

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4.5 cm
Package 1 Width	10.1 cm
Package 1 Length	19.8 cm
Package 1 Weight	0.375 kg

Offer Sustainability

EU RoHS Directive	Compliant with Exemptions
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes