

Product data sheet

Characteristics

56CV332-GY

56 Series Switched Socket Outlet - 32A - 3 Pin - 1 Pole Switch - 250V - Grey



Main

Range of product	Series 56
Range	Clipsal - 56 Series
Product brand	Clipsal
Product or component type	Socket-outlet
Device application	Power supply
Colour	Grey (RAL 7035)

Complementary

Number of poles	3
Plug, socket category	Low voltage
Outlet standard	Australian/New Zealand
Plug, socket, control station shape	Straight
Number of modules	1
Number of power socket outlets	1 protective cover
[In] rated current	32 A
[Ue] rated operational voltage	250 V AC 50 Hz
Poles description	1P + N + E
Protection type	Without protection
Device mounting	Surface
Material	Polycarbonate: cover
Contacts material	Pins: phosphor bronze
Connections - terminals	Screw terminals cable(s) 4...16 mm ²
Electrical connection	Industrial connector
Depth	108 mm
Width	101 mm
Height	204 mm
Targeted country	Australia

Environment

Standards	AS/NZS 3133 AS/NZS 3123
Ambient air temperature for operation	-25...75 °C
IP degree of protection	IP66 conforming to AS 60529

Packing Units

Package 1 Weight	1.000 kg
Package 1 Height	108.000 mm
Package 1 width	101.000 mm
Package 1 Length	204.000 mm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile