

Product data sheet

Characteristics

56CV416K-GY

Switched Socket, Clipsal - 56 Series, Vertical 4Pin 16A Hi Cycl

Main

Range	Clipsal - 56 Series
Product or component type	Switched socket
Device application	Power supply
Colour	Grey (RAL 7035)

Complementary

Plug, socket category	Low voltage
Outlet standard deviation	Australian/New Zealand
Plug, socket, control station shape	Straight Angled
[In] rated current	16 A
[Ue] rated operational voltage	500 V AC 50 Hz
Poles description	3P + E
Protection type	Without protection
Material	Polycarbonate: cover
Contacts material	Pins: phosphor bronze
Connections - terminals	Screw terminal cable(s) 1.5...16 mm ²
Mounting mode	Surface mounted
Outlet standard	Industrial
Depth	108 mm
Width	101 mm
Height	204 mm
Net weight	1.1 kg
Targeted country	Australia



Environment

Standards	AS/NZS 3123
Ambient air temperature for operation	-25...75 °C
IP degree of protection	IP66 conforming to AS 60529

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	20.4 cm
Package 1 Width	10.1 cm
Package 1 Length	10.8 cm
Package 1 Weight	1.1 kg

Offer Sustainability

EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes