

Product data sheet

Characteristics

56CV416K-GY

56 Series Switched Socket Outlet - 16A - 4 Pin - 3 Pole Switch - 500V - Grey



Main

Range	Clipsal - 56 Series
Product or component type	Switched socket
Device application	Power supply
Colour	Grey (RAL 7035)

Complementary

Plug, socket category	Low voltage
Outlet standard	Australian/New Zealand
Plug, socket, control station shape	Straight Angled
[In] rated current	16 A
[Ue] rated operational voltage	500 V AC 50 Hz
Poles description	3P + E
Protection type	Without protection
Material	Polycarbonate: cover
Contacts material	Pins: phosphor bronze
Connections - terminals	Screw terminal cable(s) 1.5...16 mm ²
Mounting mode	Surface mounted
Outlet standard	Industrial
Depth	108 mm
Width	101 mm
Height	204 mm
Net weight	1.1 kg
Targeted country	Australia

Environment

Standards	AS/NZS 3123
Ambient air temperature for operation	-25...75 °C
IP degree of protection	IP66 conforming to AS 60529

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	20.4 cm
Package 1 Width	10.1 cm
Package 1 Length	10.8 cm
Package 1 Weight	1.1 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile