

## Product data sheet

### Characteristics

# 56CV420LE-GY

## SWITCHED SOCKET VERTICAL IP66 4 PIN 20A LESS ENCLOSURE



### Main

Range of product	Series 56
Product brand	Clipsal
Device application	Power supply
Colour	Grey (RAL 7035)

### Complementary

Number of poles	4
Number of modules	3
Number of power socket outlets	1 protective cover
[In] rated current	20 A
[Ue] rated operational voltage	500 V AC
Depth	45 mm
Width	101 mm
Height	198 mm

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	0.517 kg
Package 1 Height	45 mm
Package 1 width	101 mm
Package 1 Length	198 mm

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.