

## Product data sheet

### Characteristics

# 56CV540-GY

## 56 Series Switched Socket Outlet - 40A - 5 Pin - 3 Pole Switch - 500V - Grey



### Main

|                           |                     |
|---------------------------|---------------------|
| Range of product          | Series 56           |
| Range                     | Clipsal - 56 Series |
| Product brand             | Clipsal             |
| Product or component type | Socket-outlet       |
| Device application        | Power supply        |
| Colour                    | Grey (RAL 7035)     |

### Complementary

|                                     |  |
|-------------------------------------|--|
| Number of poles                     | 5  |
| Plug, socket category               | Low voltage                                      |
| Outlet standard                     | Australian/New Zealand                           |
| Plug, socket, control station shape | Straight   |
| Number of modules                   | 3  |
| Number of power socket outlets      | 1 protective cover                               |
| [In] rated current                  | 40 A   |
| [Ue] rated operational voltage      | 500 V AC 50 Hz                                   |
| Poles description                   | 3P + N + E                                       |
| Protection type                     | Without protection                               |
| Device mounting                     | Surface  |
| Material                            | Polycarbonate: cover                             |
| Contacts material                   | Pins: phosphor bronze                            |
| Connections - terminals             | Screw terminals cable(s) 10...25 mm <sup>2</sup> |
| Electrical connection               | Industrial connector                             |
| Depth                               | 108 mm   |
| Width                               | 101 mm   |
| Height                              | 204 mm   |
| Targeted country                    | Australia  |

### Environment

|                                       |                             |
|---------------------------------------|-----------------------------|
| Standards                             | AS/NZS 3133<br>AS/NZS 3123  |
| Ambient air temperature for operation | -25...75 °C                 |
| IP degree of protection               | IP66 conforming to AS 60529 |

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

## Packing Units

|                              |          |
|------------------------------|----------|
| Unit Type of Package 1       | PCE      |
| Number of Units in Package 1 | 1        |
| Package 1 Weight             | 1.133 kg |
| Package 1 Height             | 10.8 cm  |
| Package 1 width              | 10.1 cm  |
| Package 1 Length             | 20.4 cm  |

## Offer Sustainability

|                            |   |
|----------------------------|---|
| Sustainable offer status   | Green Premium product                         |
| REACH Regulation           | <a href="#">REACH Declaration</a>             |
| EU RoHS Directive          | Compliant <a href="#">EU RoHS Declaration</a> |
| Mercury free               | Yes   |
| RoHS exemption information | <a href="#">Yes</a>                           |
| China RoHS Regulation      | <a href="#">China RoHS Declaration</a>        |
| Environmental Disclosure   | <a href="#">Product Environmental Profile</a> |