

Product data sheet

Characteristics

56CV550LE-GY

SWITCHED SOCKET VERTICAL IP66 5 PIN 50A LESS ENCLOSURE



Main

Range of product	Series 56
Product brand	Clipsal
Device application	Power supply
Colour	Grey (RAL 7035)




Complementary

Number of poles	5
Number of modules	3
Number of power socket outlets	1 protective cover
[In] rated current	50 A
[Ue] rated operational voltage	500 V AC
Depth	45 mm
Width	101 mm
Height	198 mm

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	785.0 g
Package 1 Height	10.05 cm
Package 1 width	9.95 cm
Package 1 Length	19.65 cm
Unit Type of Package 2	CAR
Number of Units in Package 2	12
Package 2 Weight	9.81 kg
Package 2 Height	21 cm
Package 2 width	34.8 cm
Package 2 Length	44.5 cm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant  EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	 Yes

China RoHS Regulation

 [China RoHS Declaration](#)

Environmental Disclosure

 [Product Environmental Profile](#)
