

Product data sheet

Characteristics

56CV710-GY

Clipsal, Switched Socket Outlet, 500V, 10A, 7 Round PIN, IP66, 3 Pole, Vertical



Main

Range of product	Series 56
Product brand	Clipsal
Device application	Power supply
Colour	Grey (RAL 7035)

Complementary

Number of poles	7
Number of modules	3
Number of power socket outlets	1 protective cover
[In] rated current	50 A
[Ue] rated operational voltage	500 V AC
Device mounting	Surface
Material	PVC (polyvinyl chloride): housing
Depth	108 mm
Width	101 mm
Height	204 mm

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	11.35 cm
Package 1 Width	10.35 cm
Package 1 Length	20.65 cm
Package 1 Weight	1065.75 g
Unit Type of Package 2	CAR
Number of Units in Package 2	12
Package 2 Height	21.0 cm
Package 2 Width	34.8 cm
Package 2 Length	44.5 cm
Package 2 Weight	13.18 kg

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Offer Sustainability

REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant with Exemptions
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins