

Product data sheet

Characteristics

56CV710-GY

Clipsal, Switched Socket Outlet, 500V, 10A, 7
Round PIN, IP66, 3 Pole, Vertical



Main

Range of product	Series 56
Product brand	Clipsal
Device application	Power supply
Colour	Grey (RAL 7035)




Complementary

Number of poles	7
Number of modules	3
Number of power socket outlets	1 protective cover
[In] rated current	50 A
[Ue] rated operational voltage	500 V AC
Device mounting	Surface
Material	PVC (polyvinyl chloride): housing
Depth	108 mm
Width	101 mm
Height	204 mm

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	11.35 cm
Package 1 Width	10.35 cm
Package 1 Length	20.65 cm
Package 1 Weight	1065.75 g
Unit Type of Package 2	CAR
Number of Units in Package 2	12
Package 2 Height	21.0 cm
Package 2 Width	34.8 cm
Package 2 Length	44.5 cm
Package 2 Weight	13.18 kg

Offer Sustainability

REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant with Exemptions
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins