

Product data sheet

Characteristics

56CVI720C-GY

56 Series Socket Outlet Interlock- Micro Switch - 20A - 7 Pin - 3P- 500V - Grey



Main

| | |
|---------------------------|---------------------|
| Range of product | Series 56 |
| Range | Clipsal - 56 Series |
| Product brand | Clipsal |
| Product or component type | Socket-outlet |
| Device application | Power supply |
| Colour | Grey (RAL 7035) |

Complementary

| | |
|-------------------------------------|---|
| Number of poles | 6 |
| Plug, socket category | Low voltage |
| Outlet standard | Australian/New Zealand |
| Plug, socket, control station shape | Straight |
| Number of power socket outlets | 1 protective cover |
| [In] rated current | 20 A |
| [Ue] rated operational voltage | 500 V AC 50 Hz |
| Poles description | 3P + N + E |
| Protection type | Without protection |
| Device mounting | Surface |
| Material | Polycarbonate: cover |
| Contacts material | Pins: phosphor bronze |
| Connections - terminals | Screw terminals cable(s) 2.5...16 mm ² |
| Electrical connection | Industrial connector |
| Depth | 108 mm |
| Width | 101 mm |
| Height | 204 mm |
| Targeted country | Australia |

Environment

| | |
|---------------------------------------|-----------------------------|
| Standards | AS/NZS 3133 AS/NZS 3123 |
| Ambient air temperature for operation | -25...75 °C |
| IP degree of protection | IP66 conforming to AS 60529 |

Packing Units

| | |
|------------------|------------|
| Package 1 Weight | 1.000 kg |
| Package 1 Height | 108.000 mm |
| Package 1 width | 101.000 mm |
| Package 1 Length | 204.000 mm |

Offer Sustainability

| | |
|----------------------------|---|
| Sustainable offer status | Green Premium product |
| REACH Regulation | REACH Declaration |
| EU RoHS Directive | Compliant EU RoHS Declaration |
| Mercury free | Yes |
| RoHS exemption information | Yes |
| China RoHS Regulation | China RoHS Declaration |
| Environmental Disclosure | Product Environmental Profile |