

## Product data sheet

### Characteristics

# 56DB2-GY

## Adaptable Enclosure, Clipsal - 56 Series, Deep, 2 Gang, 140x101x198mm



### Main

Range of product	Series 56
Range	Clipsal - 56 Series
Product brand	Clipsal
Colour	Grey (RAL 7035)
Cover type	Transparent

### Complementary

Number of gangs	2 gangs
Shape	Rectangular
Device mounting	Surface
Mounting mode	Wall-mounted
Material	PVC (polyvinyl chloride): housing
Fixing mode	By screws
Number of mounting holes	8
Length	140 mm
Width	101 mm
Depth	140 mm
Height	198 mm
Net weight	0.8 kg
IP degree of protection	IP66 conforming to AS 60529
Standards	AS 3100

### Environment

Ambient air temperature for operation	-25...75 °C
---------------------------------------	-------------

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	15.5 cm
Package 1 Width	10.0 cm
Package 1 Length	20.0 cm
Package 1 Weight	840.0 g
Unit Type of Package 2	CAR
Number of Units in Package 2	9
Package 2 Height	36.0 cm
Package 2 Width	34.5 cm
Package 2 Length	40.5 cm
Package 2 Weight	8.1 kg

## Offer Sustainability

REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>