

## Product data sheet

### Characteristics

# 56DB2L-GY

## Enclosures and Boxes, Adaptable Enclosures Covers, 2 Gang Cover only



### Main

Range	Clipsal - 56 Series
Range of product	Series 56
Product brand	Clipsal
Product or component type	DIN cover
Colour	Grey (RAL 7035)

### Complementary

Material	Polycarbonate: housing
Device mounting	Surface
Mounting mode	Wall-mounted
Width	95 mm
Height	192 mm
Depth	78 mm
Net weight	0.26 kg

### Environment

Standards	AS 3100
IP degree of protection	IP66 conforming to AS 60529
Ambient air temperature for operation	-25...75 °C

### Packing Units

Unit Type of Package 1	Db
Number of Units in Package 1	1
Package 1 Height	11.0 cm
Package 1 Width	10.8 cm
Package 1 Length	20.2 cm
Package 1 Weight	257.1 g
Unit Type of Package 2	CAR
Number of Units in Package 2	12
Package 2 Height	21.0 cm
Package 2 Width	34.8 cm
Package 2 Length	44.5 cm
Package 2 Weight	3.47 kg

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>