

Product data sheet

Characteristics

56DB3-GY

Clipsal - 56 Series, Adaptable Enclosure,
Deep, 3 Gang, 140x294x101mm



Main

Range of product	Series 56
Range	Clipsal - 56 Series
Product brand	Clipsal
Colour	Grey (RAL 7035)
Cover type	Transparent

Complementary

Number of gangs	3 gangs
Shape	Rectangular
Device mounting	Surface
Mounting mode	Wall-mounted
Material	PVC (polyvinyl chloride): housing
Fixing mode	By screws
Number of mounting holes	12
Length	140 mm
Width	101 mm
Depth	140 mm
Height	294 mm
Net weight	1.2 kg
IP degree of protection	IP66 conforming to AS 60529
Standards	AS 3100

Environment

Ambient air temperature for operation	-25...75 °C
---------------------------------------	-------------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	10.5 cm
Package 1 Width	16.0 cm
Package 1 Length	31.0 cm
Package 1 Weight	1240.0 g
Unit Type of Package 2	CAR
Number of Units in Package 2	10
Package 2 Height	47.5 cm
Package 2 Width	34.2 cm
Package 2 Length	39.0 cm
Package 2 Weight	12.4 kg

Offer Sustainability

REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant with Exemptions
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes