

Product data sheet

Characteristics

56DB6-GY

56 Series Adaptable Enclosure - 6 Gang - Grey



Main

| | |
|------------------|---------------------|
| Range of product | Series 56 |
| Range | Clipsal - 56 Series |
| Product brand | Clipsal |
| Colour | Grey (RAL 7035) |
| Cover type | Transparent |

Complementary

| | |
|--------------------------|-----------------------------------|
| Number of gangs | 6 gangs |
| Shape | Rectangular |
| Device mounting | Surface |
| Mounting mode | Wall-mounted |
| Material | PVC (polyvinyl chloride): housing |
| Fixing mode | By screws |
| Number of mounting holes | 24 |
| Length | 140 mm |
| Width | 294 mm |
| Depth | 140 mm |
| Height | 198 mm |
| Net weight | 1.84 kg |
| IP degree of protection | IP66 conforming to AS 60529 |
| Standards | AS 3100 |

Environment

| | |
|---------------------------------------|-------------|
| Ambient air temperature for operation | -25...75 °C |
|---------------------------------------|-------------|

Packing Units

| | |
|------------------------------|-----------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Weight | 1.889 kg |
| Package 1 Height | 15 cm |
| Package 1 width | 20 cm |
| Package 1 Length | 31 cm |
| Unit Type of Package 2 | CAR |
| Number of Units in Package 2 | 6 |
| Package 2 Weight | 11.502 kg |
| Package 2 Height | 42.3 cm |
| Package 2 width | 34.5 cm |
| Package 2 Length | 45.2 cm |

Offer Sustainability

| | |
|----------------------------|---|
| Sustainable offer status | Green Premium product |
| REACH Regulation | REACH Declaration |
| EU RoHS Directive | Compliant EU RoHS Declaration |
| Mercury free | Yes |
| RoHS exemption information | Yes |
| China RoHS Regulation | China RoHS Declaration |
| Environmental Disclosure | Product Environmental Profile |