

Product data sheet

Characteristics

56DB6BASE-GY

Adaptable Enclosure, Clipsal - 56 Series, 6 Gang

Main

Range	Clipsal - 56 Series
Product or component type	Adaptable enclosure
Colour	Grey (RAL 7035)

Complementary

Device mounting	Surface
Mounting mode	Wall mount
Material	Polycarbonate: housing
Length	294 mm
Width	198 mm
Depth	63 mm
Net weight	1 kg
IP degree of protection	IP66 conforming to AS 60529
Standards	AS 3100

Environment

Ambient air temperature for operation	-25...75 °C
---------------------------------------	-------------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	29.9 cm
Package 1 Width	6.8 cm
Package 1 Length	20.0 cm
Package 1 Weight	1307.0 g
Unit Type of Package 2	CAR
Number of Units in Package 2	7
Package 2 Height	21.0 cm
Package 2 Width	34.8 cm
Package 2 Length	44.5 cm
Package 2 Weight	9.534 kg

Offer Sustainability

Packaging without single use plastic	No
Packaging made with recycled cardboard	Yes
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Take-back	No
Carbon footprint (kg.eq.CO2 per CR, Total Life cycle)	9