

Product data sheet

Characteristics

56DOL12/1S-GY

Clipsal - 56 Series, DOL Motor Starter, 5.5kW, 415V, 2 Push Button, Switch Version



Main

Range of product	Series 56
Product or component type	Switch
Colour	Cover: grey

Complementary

Colour code	GY
Motor starter type	Direct on line
Control type	Push-button
[Us] rated supply voltage	415 V AC 50 Hz
Network type	AC
Rated operational power in W	5.5 kW at 415 V (AC-3)
[Ie] rated operational current	12 A
Overload current	9...13 A
Connections - terminals	Screw terminal solid Screw terminal stranded
Tightening torque	0.8 N.m
Network number of phases	3 phases
Product destination	2 push-button
Height	294 mm
Width	101 mm
Net weight	1.52 kg
Targeted country	Australia
Market segment	Industry Small commercial Utility

Environment

Suitability for isolation	No
IP degree of protection	IP66 conforming to AS 60529
Ambient air temperature for operation	-25...75 °C
Standards	AS/NZS 3133 AS/NZS 3100

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	1.52 kg

Offer Sustainability

REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant with Exemptions
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes