

Product data sheet

Characteristics

56DOL12/LO-GY

56 Series - Direct Online Starter - 3 Phase -
5.5kW - 415V - grey



Main

Range of product	Series 56
Product or component type	Switch
Colour	Cover: grey

Complementary

Colour code	GY
Motor starter type	Direct on line
Control type	Push-button
[Us] rated supply voltage	415 V AC 50 Hz
Network type	AC
Rated operational power in W	5.5 kW at 415 V (AC-3)
Connections - terminals	Screw terminal solid Screw terminal stranded
Tightening torque	0.8 N.m
Height	204 mm
Width	101 mm
Product weight	1.311 kg
Targeted country	Australia
Market segment	Utility Small commercial Industry

Environment

Suitability for isolation	No
IP degree of protection	IP66 conforming to AS 60529
Ambient air temperature for operation	-25...75 °C
Standards	AS/NZS 3100 AS/NZS 3133

Packing Units

Package 1 Weight	1.311 kg
------------------	----------

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile