

Product data sheet

Characteristics

56DOL12/LOB-GY

56 Series 240V Motor Starter. Temperature Range minus 25C to +75C



Main

Range of product	Series 56
------------------	-----------

Complementary

Colour code	GY
Motor starter type	Direct on line
[Us] rated supply voltage	415 V AC 50 Hz
Network type	AC
Rated operational power in W	5.5 kW at 400 V (AC-3)

Environment

Ambient air temperature for operation	-20...60 °C
---------------------------------------	-------------

Packing Units

Unit Type of Package 1	Db
Number of Units in Package 1	1
Package 1 Weight	1.316 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.