

Product data sheet

Characteristics

56DOL16/LO-GY

Motor Starter, Clipsal - 56 Series, Temperature Range -25C to +75C, 415V

Main

Range of product	Series 56
Product or component type	Switch
Colour	Cover: grey

Complementary

Colour code	GY
Motor starter type	Direct on line
Control type	Push-button
[Us] rated supply voltage	415 V AC 50 Hz
Network type	AC
Rated operational power in W	7.5 kW at 415 V (AC-3)
Connections - terminals	Screw terminal solid Screw terminal stranded
Tightening torque	0.8 N.m
Height	204 mm
Width	101 mm
Net weight	1.327 kg
Targeted country	Australia
Market segment	Industry Small commercial Utility

Environment

Suitability for isolation	No
IP degree of protection	IP66 conforming to AS 60529
Ambient air temperature for operation	-25...75 °C
Standards	AS/NZS 3100 AS/NZS 3133

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	15.5 cm
Package 1 Width	10 cm
Package 1 Length	20 cm
Package 1 Weight	1257 g

Offer Sustainability

EU RoHS Directive	Compliant with Exemptions
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes