

Product data sheet

Characteristics

56DOL22/1R-GY

56DOL22/1R RESET DOL 3PH 11KW. TEMPERATURE RANGE -25C TO +75C



Main

Range of product	Series 56
------------------	-----------

Complementary

Colour code	GY
Motor starter type	Direct on line
[Us] rated supply voltage	415 V AC 50 Hz
Network type	AC
Rated operational power in W	11 kW at 400 V (AC-3)
[Ie] rated operational current	25 A
Overload current	16...24 A
Network number of phases	3 phases
Product destination	1 push-button

Environment

Ambient air temperature for operation	-20...60 °C
---------------------------------------	-------------

Packing Units

Package 1 Weight	1.800 kg
------------------	----------

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins