

## Product data sheet

### Characteristics

# 56DOL9/1S-GY

## DOL MOTOR STARTERS 3PH 4 KW

## TEMPERATURE RANGE -25 C TO +75 C



### Main

Range of product	Series 56
------------------	-----------

### Complementary

Colour code	GY
Motor starter type	Direct on line
[Us] rated supply voltage	415 V AC 50 Hz
Network type	AC
Rated operational power in W	4 kW at 400 V (AC-3)
[Ie] rated operational current	9 A
Overload current	0.63...1 A
Network number of phases	3 phases
Product destination	2 push-button

### Environment

Ambient air temperature for operation	-20...60 °C
---------------------------------------	-------------

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	0.001 kg