

Product data sheet

Characteristics

56DOL9/1V6R-GY

56 DOL 9/1 V 6R RESET DOL 3PH 4 KW

TEMPERATURE RANGE -25 C TO +75 C

Main

Range of product	Series 56
------------------	-----------

Complementary

Colour code	GY
Motor starter type	Direct on line
[Us] rated supply voltage	415 V AC 50 Hz
Network type	AC
Rated operational power in W	4 kW at 400 V (AC-3)
[Ie] rated operational current	9 A
Overload current	1...1.6 A
Network number of phases	3 phases
Product destination	1 push-button

Environment

Ambient air temperature for operation	-20...60 °C
---------------------------------------	-------------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	4.98 kg