

## Product data sheet

### Characteristics

# 56DOL9/1V6S-GY

DOL Motor Starter, Clipsal - 56 Series, 4kW, 415V, 2 Push Button, Switch Version, LRD06

### Main

Range of product	Series 56
Product or component type	Switch
Colour	Cover: grey

### Complementary

Colour code	GY
Motor starter type	Direct on line
Control type	Push-button
[Us] rated supply voltage	240 V AC 50 Hz
Network type	AC
Rated operational power in W	4 kW at 240 V (AC-3)
[Ie] rated operational current	9 A
Overload current	1...1.6 A
Connections - terminals	Screw terminal solid Screw terminal stranded
Tightening torque	0.8 N.m
Network number of phases	3 phases
Product destination	2 push-button
Height	294 mm
Width	101 mm
Net weight	4.98 kg
Targeted country	Australia
Market segment	Utility Industry Small commercial


### Environment

Suitability for isolation	No
IP degree of protection	IP66 conforming to AS 60529
Ambient air temperature for operation	-25...75 °C
Standards	AS/NZS 3100 AS/NZS 3133

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	4.98 kg

## Offer Sustainability

EU RoHS Directive	Compliant with Exemptions
China RoHS Regulation	 <a href="#">China RoHS Declaration</a>
RoHS exemption information	 <a href="#">Yes</a>